



# Product Information

[www.miller-stephenson.com](http://www.miller-stephenson.com)

## MS-114D Conformal Coating Stripper

### Description

This stripper is specifically formulated to remove Miller-Stephenson's (MS) conformal coatings. MS-114D Conformal Coating Stripper will dissolve MS's Silicone Coatings, Urethane Coatings, Acrylic Coatings, and Varnish Coating from many types of electronic circuitry.

MS-114D safely dissolves these coatings without causing damage to most electronic components and elastomers. It will attack ABS, acrylic and polystyrene. Compatibility with plastic materials should be tested before use.

### ADVANTAGES:

- Nonflammable
- Fast, effective coating removal
- Safe for printed circuit boards
- Contains no ozone depleting chemicals (ODC)
- RoHS compliant
- Available in quart and gallon containers

### PHYSICAL PROPERTIES:

Color.....Clear to light yellow  
Boiling point.....118°F/48°C  
Vapor pressure.....214 mm Hg @ 68°F/20°C  
Density.....1.25g/cc @ 77°F  
VOC Content.....903 gms/l  
Flash point.....None  
Form.....Liquid

### Directions for Use:

To remove silicone, acrylic, urethane and varnish coatings:

Soak for about thirty minutes or more, then rinse thoroughly with alcohol. For urethane and varnish coatings it may be necessary to soak for several hours before the coatings will break up or dissolve.

MS-114D is very volatile. Therefore, it is necessary to keep it in a closed container when soaking. Use in a well-ventilated area.

Safety Data Sheet (SDS) is available upon request.

1623-4M

The recommendation made here with and the information set forth with respect to the performance or use of our products are believed, but not warranted to be accurate. The products discussed are sold without warranty, as to fitness or performance, express or implied and upon condition that purchasers shall make their own test to determine suitability of such products for their particular purposes. Likewise, statements concerning the possible uses of our products are not intended as recommendations to use our products in the infringement of any patent.

For technical information call 800.992.2424 or 203.743.4447  
For product sales: CT 800.442.3424, CA 800.771.8161, IL 800.447.4866, Canada 800.307.2199  
[www.miller-stephenson.com](http://www.miller-stephenson.com)